

Punti di forza dello STAMPO ISOSTATICO CALIBRA - Vantaggi qualitativi

PIASTRELLE MONOCALIBRO

- Ottimizzazione scorta di magazzino
- Possibilità di produrre strutture di diverse profondità, ottenendo unico calibro
- Riduzione costi di gestione

Il dispositivo isostatico CALIBRA può essere applicato sia a stampi superiori che inferiori del tipo SMF, a seconda delle necessità del cliente, legate a caratteristiche di prodotto o all'altimetria della pressa.

Indipendentemente dalla posizione di applicazione, lo stampo CALIBRA garantisce un funzionamento ed un prodotto pressato ottimale



Highlights of GAPE DUE CALIBRA MOULD - Quality advantage

MONOCALIBER TILES

- Optimization of tile's stock
- Possibility to produce reliefs with different depths yet maintaining just one single caliber
- Reduction of the management costs

The isostatic device CALIBRA can be applied to both the upper and lower SMF moulds, depending on the needs of the client, related to the characteristics of the tile product or the space available on the press.

Regardless of the upper or lower application, the mould CALIBRA guarantees a trouble-free functioning and faultless pressed product

